



Ultrasonic Cleaner 150I

RA series is dual-frequency ultrasonic cleaner 150I machine suitable for industrial applications. The core component ultrasonic generator adopts the most advanced T technology platform which has high cleaning efficiency, simple operations and no need of debugging on site. Ultrasonic cleaner 150I can be widely used in metal products, auto parts, electronics cleaning, medical instruments, optical glass cleaning etc.

Ultrasonic Cleaner 150I Manufacturers and Suppliers From China

1.Ultrasonic Cleaner 150I Introduction

RA series is dual-frequency ultrasonic cleaner 150I machine suitable for industrial applications. The core component ultrasonic generator adopts the most advanced T technology platform which has high cleaning efficiency, simple operations and no need of debugging on site. Ultrasonic cleaner 150I can be widely used in metal products, auto parts, electronics cleaning, medical instruments, optical glass cleaning etc.



Clangsonic ultrasonic cleaner are mainly used in industry. Size and power can be customized by your request.



Clangsonic provides varies of capacities of ultrasonic cleaner. Please contact us for customized tank size.

2.Ultrasonic Cleaner 150l Parameter (Specification)

Name	Ultrasonic Cleaner With Lifting System			
Model	RA85	RA120	RA160	Customizable 200-1000L
Ultrasonic Frequency	25/45kHz, 28/68kHz, 40/80kHz, 40/130kHz or 80/130kHz			
Ultrasonic Power	1500Watts	1800Watts	2400Watts	-
Ultrasonic Power Adjustable	10-100%			
Inner Tank Size	600x400x350mm	650x450x400mm	700x500x450mm	-
Basket Size	520x300x150mm	570x350x200mm	620x400x250mm	-
Overall Size	720x850x1600mm	770x900x1600mm	890x950x1600mm	-
Heating Power	5000Watts	6000Watts	8000Watts	-
Heating Temperature	30-80°C			
Timing	0-60min. or Normally Open			
Power Supply	380V/50Hz, 3 Phase 5 Wire			
Power Supply Cable Length	3m			
SUS Cover	Optional			
Circulation System	Optional			
Oil Skimmer	Optional			

3. Ultrasonic Cleaner 150l Features and Application

1. One Button Start

Press “Start” button to complete the functions of basket lift in, basket oscillation, ultrasonic cleaning and basket lift out etc.

2. Oscillation System

The basket with workpiece will be moved up and down automatically during cleaning, that will avoid dirt accumulating on surface or holes of workpiece and improve cleanliness.

3. Dual-Frequency

2 frequencies can be switched easily as you need. For different cleaning process, you can choose different frequency, and it is also very suitable for workpiece which needs both coarse and fine cleaning.

4. Automatic Sweep

Sweep function can eliminate the standing waves effectively. That’s helpful to improve ultrasonic distribution in the tank and make cleaning more uniformly.

5. 2 Times Peak Power

2 times peak power excitation can act on stubborn stains and semi-aqueous solvents, ultrasonic performance is improved obviously.

6. Linearly Adjustable Power

Ultrasonic power can be adjusted 10-100% linearly, which is more precisely for different cleaning requests.

7. Load Self-Adaption

It will adjust itself to fit to different working conditions (Liquid Temperature, Liquid Level and Workpiece) automatically, and maintain the optimal working frequency and constant power output.

8. High Definition Industrial Level LCD Display

User-friendly LCD display allows user to monitor working status and set parameters.

9. Efficient Cleaning

Adopting peak modulation technology which can breakdown the bubbles more quickly and remove the stubborn stains easily. Under same conditions, the breakdown speed of foil is significantly improved.

10. Stable Output

Self-adaption technology can ensure the machine to fit to load changing perfectly, such as different liquid level, liquid temperature changing and workpiece movement. Ultrasonic performance will keep still.

11. High Conversion Efficiency

The conversion efficiency of ultrasonic and electric energy is more than 90%. The energy conservation is more than others at same ultrasonic power output.

12. Extended Function

Circulation System, Oil Separator, Bubbling Tank, Rinsing

clangsonic

Cleanness is endless


Application:

The ultrasonic cleaning machine is suitable for cleaning circuit boards, bearing components, optical lenses, motorcycle part, ion plating part, electroplating parts, audioprefixes, clock parts, semiconductor wafers, magnetic materials, polyester.

1. Jewelry (Jewels, Jade, Gold and Silver)



2. Auto parts (Cylinder Block, Bearing, Valve body and so on)





3. Precision parts (Mobile Accessories, Watch parts)



4. Material (Steel, Cooper, Plastic,)



5. Optical and electronics (Semiconductor, Optical lens, Electronic parts,)




6. Appliance Application (Fruit, Stainless Steel Cutlery, Crockery)



4. Details Images





clangsônic

www.clangsonicultrasonics.com

clangsônic




Tel:+86-576-87276622

Email:info@clangsonic.com



Optional Circulation System With Oil Skimmer



Equipped With Circulation System And Oil Skimmer

5. Company Qualification

clangsonic

Yuhuan Clangsonic Ultrasonic Co., Ltd. is a professional engaged in ultrasonic transducer, ultrasonic shock box, ultrasonic (generator) power and ultrasonic equipment research and application of the manufacturer.

Since 2003 the company since its establishment, unswervingly adhere to the higher quality and better service as our ultimate goal.

Our products are exported to the world more than 40 countries and regions. To provide customers with a full range of ultrasonic products and solutions, so that waves of the company to become a global customer real partners.



The company has an effective construction area of over 6,000 square meters, with imported Tian Tian, Baichao sheet metal bending machine, KUKA robot, as well as the Swedish fuse factory, and CNC sawing machine, CNC lathe, CNC milling machine and other equipment, making the product more reliable.

Visit Factory



Workshop



Exhibition





6. Deliver, Shipping and Serving





To better ensure the safety of your goods, professional, environmentally friendly, convenient and efficient packaging services will be provided.

CLANGSONIC

Shipping & Payment

Started working again,Started working again,Started working again.



7. FAQ

1. Are you manufacturer or trading company?

We are manufacturer. All the core components (ultrasonic transducer, ultrasonic generator) are home-made by ourselves.

2. Do you accept OEM and ODM?

Yes, we also have profession R&D teams (ultrasonic transducer team, ultrasonic generator team and mechanical design team) to responds your special needs quickly.

3. Delivery time

Standard products can be delivered within 7 working days. Customized machine depend on the design.

4. Warranty

We guarantee quality of the products for a period of 1 year. If any quality problem within warranty, we'll provide free spare parts or repairing service.

5. Do you provide trial cleaning service?

Yes, you're welcome to send the workpieces for trial cleaning. We'll send you video and report about the test. It's free service.

6. Can you provide ultrasonic transducer or generator if any failure?

Yes, ultrasonic transducer and ultrasonic generator are designed and manufactured by ourselves. We can send the right parts quickly for replacement.

7. Payment Methods?

T/T ,L/C, D/P ,D/A, West Union , Paypal, MoneyGram ,Escrow .

8. Which frequency and power is suitable for our workpiece?

Please contact us and provide details as specific as you can. Information includes: the size, material, weight and dirt of your workpiece and cleaning tank dimension etc.